Portable [condition monitoring] OICMS PRO + HDV

[ON-SITE PORTABLE SERIES]

OilCMS is the portable, robust, realtime solution featuring Atten[2] optical technology for particle counting and particle morphology analysis in lubrication systems.

The Portable OilCMS utilizes breakthrough digital imaging technology which provides a greater insight into the size and type of particulate in any oil system. Air bubble elimination and shape recognition gives root cause particle analysis. A stepper motor pump for high viscosity oils completes the package.

Giving ISO 4406 counts as well as 4, 6, 14, 21, 38 & >70 micron sizing and bubble elimination. Digital imaging combined with advanced algorithms sorts particles into fatigue wear, cutting wear and sliding wear categories to give root cause analysis.

This powerful technology, when coupled with additional sensors for measuring water content and viscosity & density, gives unprecedented on the spot insight into the condition of your oil.

All Atten[2] technology functionalities available:

- Particle counting according to ISO 4406 standard > 4 microns
- Discrimination and counting of air bubbles
- Classifies particles in 6 ranges (>4, >6, >14, >21, >38, >70 μm)
- Shape analysis

+ Humidity (%RH)

+ Viscosity & Density *

*kynematic & dynamic




[FEATURES]



Digital Imaging Particulate Counter

Classification and counting of particles larger than 4 microns in 6 ranges. 4, 6, 14, 21, 38, 70 & >100 microns. Air bubble and water droplet elimination.




Viscosity

Displays live kinematic and dynamic viscosities plus reference viscosity at 400.



Root cause information

Shape determination to classify fatigue, sliding or cutting wear as well as fibre identification helping to identify the root cause.



Water sensor

Inbuilt water sensor that provides early diagnosis, reducing potential failures associated with water presence in lubrication and hydraulic systems, improving machine and process reliability.

1	Î.		
Fluid Compatibility	Synthetic oils, organic oils, mineral oils & diesel fuel (2,400 cSt viscosity limit)		
Display Information	Particulate: ISO 4406, SAE AS4059 & NAS 1638, bubble elimination and particle wear analysisWater: relative humidity (RH%).Viscosity:Range: 25-400mPa.sResolution: 0.1mPa.sAccuracy.+/-5%Density:Range: 0.6kg/m3 - 1.3kg/m?Resolution: 0.001kg/m3Accuracy: +/- 2%		
Modes of operation	of operationHigh-pressure live system sampling (up to 350 bar) - via a high-pressure adaptor Bottle sampling and tank sampling (up to 2,5 bar)		
Data	All data stored locally and backed up off-site. Export to .cSV or PDF		

[TECHNICAL INFORMATION]

[DIMENSIONS]



Atten[2]

[TOUCH SCREEN DISPLAY]

1.	ISO: 18 / 1	6 / 13	04/02/2022 14:38:02	4.
2.	Size ISO 4μm 18.6 6μm 16.2 14μm 13.4 21μm 11.5 38μm 9.3 70μm 8.2	Particles Bubbles 1921 4 364 3 54 2 15 2 3 1 1 0	20.0 17.5 15.0 12.5 10.0 2.0 5.6 9.2 12.8 16.4 20.0 Time (Secs)	5.
3.		Viscosity: 188 mPa RH: 56%, 22°	.S 4µm 6µm 14µm 14µm 14µm 14µm 14µm 14µm 14µm 14	6.

- Clear and easy to read ISO code which changes between green, 1. white and red to indicate the oil cleaninliness
- Oil cleanliness for each size category details the ISO code, number 2. of particles per mililitre and the bubbles detected
- Additional sensors give an unprecedent insight into the overall 3. condition of the oil
- Additional settings allow control of the pump speed for priming and 4. flushing, datalogging, ISO cleanliness alarm limits and changing the time zone
- Oil cleanliness is trended over time to show how its condition 5. changes
- Particles are analysed and sorted into fatigue wear, cutting wear, 6. sliding wear and fibre identification to give root cause analysis



Internal Stepper Motor Pump

We've developed a fully controllable stepper motor driven pump to deliver exact flow rates for any oil from 1 to 2,400 cSt. The pump also allows connection to a live system up to 350 bar via a high pressure adaptor.



Battery life

Internal rechargeable lithium battery provides a long life for remote use.